


Isopropanol Purity on ZB-624 30x0.32x1.8**Column:** Zebron[™] ZB-624, GC Cap. Column 30 m x 0.32 mm x 1.80 μ m, Ea**Phase:** 6% Cyanopropylphenyl 94% Dimethylpolysiloxane**Dimensions:** 30 meters x 0.32 mm x 1.8 μ m**Order No:** 7HM-G005-31**Oven Profile:****Carrier Gas:** Constant Flow Helium, 1.5 mL/min**Injection:** Split 15.0000000000:1 0 μ L @ 150°C**Detection:** Refractive Index (0°C)**Analyst Note:** Ethanol at 0.5% concentration was used as the internal standard. RSD values for water were calculated at 1.8% with n = 3. Detector was turned off for isopropanol solvent peak at 3.3 min to 4.0 min to prevent detector**Products used in this application:****ANALYTES:**

- 1 Water
- 2 Ethanol

